

4460 Consumables

KIT,OE,A,4460-KIT A Argon Circuit MBS Stand 402 & 402R for 4460

CE-AA23946	Oring D2x1.5	Quantity 10	Replace as Required
CE-AA24342	Oring D6x2	Quantity 10	Replace as Required
CE-AA20455	Oring D13x1.5	Quantity 10	Replace at PM

KIT,OE,B,4460-KIT B MBS 402 Stand for 4460

CE-AA25389	Oring D11x3	Support/Table	Replace at PM
CE-AA25643	Oring D14x2	Channel/Tube	Replace at PM
CE-AA26160	Oring D27x3	Channel/Lens Holder	Replace at PM
CE-AA20336	Oring D10x2	Channel/Shutter	Replace at PM

KIT,OE,C-OE KIT C Cabinet and Ventilation (2460/3460/4460)

CE-A028610	Filter for Cabinet and Ventilation (2 Required for 4460)		Replace at PM
------------	--	--	---------------

KIT,OE,D-OE KIT D Argon Filter and Cartridge (2460/3460/4460)

CE-A037260	OIL,VACUUM PUMP,CMP ELITE Z	Vacuum Systems Only	Replace at PM
------------	-----------------------------	---------------------	---------------

KIT,OE,E-OE KIT E Spectrometer Oring Kit (2460/3460/4460)

CE-AA15037	Oring D13.95x2.62	Air Inlet Valve	Replace as Required
CE-AA19710	Oring D26.2x3	PTM Oring	Replace as Required
CE-AA20227	Oring D85x3	Cover	Replace as Required
CE-AA70526	Oring D 32.93x3.53	Cover	Replace as Required
CE-A028214	Oring D90x3	Holder to Spectro Ring	Replace as Required
CE-AA20059	Oring D100x5	Cover Oring	Replace as Required
CE-A029120	Oring D24x2	Electrical Connector	Replace as Required
CE-AA19786	Oring D545.47x7	Fatigue Lamp Electrical Connector	Replace as Required
CE-AA22637	Oring D32.99x2.62		Replace as Required
CE-AA20979	Oring D32x2.5	Reflected Beam Cover	Replace as Required
CE-A029432	Oring D171.05x3.53	Mirror Access Cover	Replace as Required